# S E R V I C E N O T E

SUPERSEDES: None

# J3972A OC3 ATM WanProbe

**Serial Numbers:** 0000A00000 / 9999Z99999 prior to EC05

# Failure of adhesive on RFI gasket material on the RFI shield.

**To Be Performed By:** Agilent-Qualified Personnel

## **Parts Required:**

P/N	Description	Quantity
5002-4539	RFI Shield	1

### **Situation:**

There exists the possibility of the adhesive which holds the gasket material to the RFI shield to fail. This causes a sagging of the conductive gasket. When the gasket material sags there is contact with the rear panel LED's. This DOES NOT cause faulty operation of the instrument, only faulty operation of LED's.

### **Solution / Action:**

Replacing the defective RFI shield with an improved design, eliminates the possibility of sagging as adhesive is not used in its' construction.

DATE: January 2001

# ADMINISTRATIVE INFORMATION

SERVICE NOTE CLASSIFICATION:  MODIFICATION AVAILABLE			
ACTION CATEGORY:	AGREEABLE TIME	☐ PERFORMANCE ENHANCEMENT ■ SERVICE/RELIABILITY ENHANCEMENT	
LOCATION CATEGORY:	☐ CUSTOMER INSTALLABLE☐ ON-SITE☐ SERVICE CENTER	AVAILABLE UNTIL: January 2003	
AUTHOR: DM	ENTITY: 0804	ADDITIONAL INFORMATION:	

© 2000 AGILENT TECHNOLOGIES PRINTED IN U.S.A.

