# Modification Available Performance Enhancement Service Note

Supersedes: N1092D-02

# N1092D DCA-M Sampling Oscilloscope

Serial Numbers: US56020051-US56020055, US56140301-US56140321, US56140328-US56140370, US56140374, US57110101-US57110108, US57110110-US57110142, US57110144-US57110167, US57110173-US57110178, US57220101-US57220108, US57220110-US57220121, US57220123-US57220145, US57220147-US57220159, US57220161-US57220169, US57220173, US57220177-US57220183, US57220185-US57220295, US57220297, MY58360101-MY58360113, MY58360118, MY58360120-MY58360123, MY58360126-MY58360156, MY58360158-MY58360161, MY59250101-MY59250107, MY59250109-MY59250127, MY59250130-MY59250145, MY59250101-MY59250151, MY59250153-MY59250197, MY59250199-MY59250212, MY59250246-MY59250278, MY59250281-MY59250308, MY59250311, MY59250312, MY59250315-MY59250402, MY59250404-MY59250420, MY59250434-MY59250637, MY59250640-MY59250643, MY59250647-MY59250649, MY59250651, MY59250652, MY59250655, MY59250656, MY59250665-MY59250670, MY59250673-MY59250681, MY59250687-MY59250690, MY59250696-MY59250723, MY59250729-MY59250742, MY59250747-MY59250761

An improved extinction ratio calibration is available for DCA-M Sampling Oscilloscopes with option 30A

Parts Required: NONE

#### ADMINISTRATIVE INFORMATION

XX Calibration Required [[]] Calibration NOT Required PRODUCT LINE: 8F AUTHOR: MM

ADDITIONAL INFORMATION:



© Keysight Technologies 2015-2023 Modification Available Service Note Version 1.3 | October 12, 2023| Page **1** of **5** 

# Situation:

With the introduction of option 40A to the N1092x DCA-M Sampling Oscilloscope product family, an improved extinction ratio (ER) calibration was introduced.

- All N1092x DCA-M instruments with <u>option 40A</u> shipped from the factory with the improved ER calibration.
- Beginning with serial number MY61270000, all N1092x DCA-M instruments with <u>option 30A</u> have been manufactured with the improved ER calibration.

The improved calibration provides:

- Improved ER measurement accuracy for NRZ signals
- Calibrated Outer ER measurements for PAM-4 signals (previously uncalibrated)

The serial numbers listed below shipped from the factory with an older version of ER calibration and differences in ER measurements can be expected as a result. To confirm the calibration version, see 'Identifying ER Calibration Version' below.

## Solution/Action:

N1092x-30A instruments with the older ER calibration will have the improved ER calibration applied during service, either:

• <u>During repair</u>. After any hardware is replaced, a new ER calibration is required, and the improved ER calibration will be performed.

or

• <u>Upon request during calibration</u>. ER calibration is normally not performed during calibration. To request the improved ER calibration, reference this service note when opening a service order.

While no additional charges will be added for ER calibration, the customer may still be charged for calibration and/or repair of unrelated failures, per the standard process.

### Identifying ER Calibration Version:

For N1092x DCA-M instruments with option 30A, units with the improved ER calibration are identified in the Help > About dialog with a "C1" annotation following the serial number.

- If the "C1" annotation is present, the unit has the improved ER calibration
- If the "C1" annotation is not present, the unit has the older ER calibration



Note that the "C1" annotation is NOT used for units with option 40A because all units have the improved ER calibration.

#### Achieving Correlation to Older ER Measurements:

For <u>NRZ signals</u>, if correlation is desired to measurements made based on the older ER calibration, an extinction ratio correction factor (ERCF) can be used (Measure > Configure Base Measurements > Extinction Ratio). It is acceptable to for users to calculate the desired ERCF based on their own DUT measurements. Alternately, the following suggested values may be used:

Filter Rate (GHz)	ERCF (%)
25.78125	2.2
26.5625	2.2
27.952493	2.5
28.05	2.5

When entered for units with the improved ER calibration, these values will adjust the new ER measurements to be closer to what would have been measured with the older calibration method.

Configure Measurements		- ? Close
Top-Base Definition Thresholds Eye Boundary	Extinction Ratio	TDEC/VECP
Extinction Ratio Correction Factor Source:		
Channel 1A: ERCF Enabled		
Apply Channel 1A Correction Factor		
NRZ Correction Factor:		
2.20 %		
PAM Correction Factor (Outer ER):		
Display ERCF Values		

No ERCF is available for <u>PAM-4 signals</u> because the Outer ER measurement was previously uncalibrated.

Date	Service Note Revision	Author	Reason for Change
06 August 2021	01	MM	As Published
11 October 2023	02	NC	Removed the notes that this could only be performed at facility with repair capability.